3M Flap disc Cubitron II 967A

CUBITRANII

Design: Precision formed ceramic grain (Cubitron? II), in high-strength synthetic resin bonding connected to the convex glass cloth plate. The individual grains of the ceramic Cubitron? II abrasives are small, preciselyshaped triangles, perpendicular in arrangement, and uniform in size. Tough grinding with highest removal rate, with up to 30 % faster removal. Grinding-activated additives prevent clogging and make for cooler grinding. Standard bore 22.23 mm.

Application: In all metal-processing areas, where high removal rates combined with very good surface finishes need to be achieved.

Characteristics

Series: Cubitron **Type: 967A**

Description	Article
Cubitron™ II Flap Disc 967A	12739442
Flap disc 967A 125mm conical P 60+	12739439
Flap grinding wheel 967A curved 125mm K40	12739436

Disclaimer: The content of this document has been composed with the utmost care. However, it is possible that certain information changes over time, becomes inaccurate or incomplete. ERIKS does not guarantee that the information provided on this document is up to date, accurate and complete; the information provided is not intended to be advice. ERIKS shall never be liable for damage resulting from the use of the information provided.

Page 1/1

PR1444295466152_EN_20.05.2024