



FESTO Semi-Rotary drive DSM-B

Characteristics

Series: DSM-B

Function: Double acting

Housing material: Aluminium alloy

Operating temperature: -10 / 60 °C

Manufacturer ID	Cushioning	Construction size	Port Size mm	Port Size in	Operating pressure bar	Article
DSM-12-270-P1-FW-A-B	Mechanical	12	M 5		2 / 10	DSM-12-270-P1-FW-A-B
DSM-12-270-P1-A-B	Mechanical	12	M 5		2 / 10	DSM-12-270-P1-A-B
DSM-16-270-P1-HD-A-B	Mechanical	16	M 5		1.8 / 10	DSM-16-270-P1-HD-A-B
DSM-16-270-P1-FW-A-B	Mechanical	16	M 5		1.8 / 10	DSM-16-270-P1-FW-A-B
DSM-16-270-P-FW-A-B	Mechanical	16	M 5		1.8 / 10	DSM-16-270-P-FW-A-B
DSM-25-270-P-A-B	Mechanical	25	M 5		1.5 / 10	DSM-25-270-P-A-B
DSM-25-270-P1-A-B	Mechanical	25	M 5		1.5 / 10	DSM-25-270-P1-A-B
DSM-T-32-270-P-A-B	Mechanical	32		G1/8	2 / 10	DSM-T-32-270-P-A-B
DSM-32-270-P1-A-B	Mechanical	32		G1/8	1.5 / 10	DSM-32-270-P1-A-B
DSM-40-270-P1-FW-A-B	Mechanical	40		G1/8	1.5 / 10	DSM-40-270-P1-FW-A-B
DSM-40-270-P-FW-A-B	Mechanical	40		G1/8	1.5 / 10	DSM-40-270-P-FW-A-B
DSM-40-270-P1-A-B	Mechanical	40		G1/8	1.5 / 10	DSM-40-270-P1-A-B
DSM-40-270-P1-HD-A-B	Mechanical	40		G1/8	1.5 / 10	DSM-40-270-P1-HD-A-B
DSM-63-270-P1-HD-A-B	Mechanical	63		G1/4	1.5 / 10	DSM-63-270-P1-HD-A-B
DSM-63-270-P-A-B	Mechanical	63		G1/4	1.5 / 10	DSM-63-270-P-A-B
DSM-12-270-CC-FW-A-B	Shock absorber	12	M 5		2 / 10	DSM-12-270-CC-FW-A-B
DSM-16-270-CC-FW-A-B	Shock absorber	16	M 5		1.8 / 10	DSM-16-270-CC-FW-A-B
DSM-25-270-CC-FW-A-B	Shock absorber	25	M 5		1.5 / 10	DSM-25-270-CC-FW-A-B
DSM-25-270-CC-HD-A-B	Shock absorber	25	M 5		1.5 / 10	DSM-25-270-CC-HD-A-B
DSM-32-270-CC-A-B	Shock absorber	32		G1/8	1.5 / 10	DSM-32-270-CC-A-B
DSM-40-270-CC-FW-A-B	Shock absorber	40		G1/8	1.5 / 10	DSM-40-270-CC-FW-A-B
DSM-40-270-CC-HD-A-B	Shock absorber	40		G1/8	1.5 / 10	DSM-40-270-CC-HD-A-B
DSM-63-270-CC-FW-A-B	Shock absorber	63		G1/4	1.5 / 10	DSM-63-270-CC-FW-A-B
DSM-12-270-A-B	Without	12	M 5		2 / 10	DSM-12-270-A-B
DSM-16-270-HD-A-B	Without	16	M 5		1.8 / 10	DSM-16-270-HD-A-B
DSM-16-270-FW-A-B	Without	16	M 5		1.8 / 10	DSM-16-270-FW-A-B
DSM-25-270-FW-A-B	Without	25	M 5		1.5 / 10	DSM-25-270-FW-A-B
DSM-32-270-FW-A-B	Without	32		G1/8	1.5 / 10	DSM-32-270-FW-A-B
DSM-40-270-FW-A-B	Without	40		G1/8	1.5 / 10	DSM-40-270-FW-A-B
DSM-40-270-A-B	Without	40		G1/8	1.5 / 10	DSM-40-270-A-B
DSM-40-270-HD-A-B	Without	40		G1/8	1.5 / 10	DSM-40-270-HD-A-B
DSM-63-270-HD-A-B	Without	63		G1/4	1.5 / 10	DSM-63-270-HD-A-B
DSM-63-270-A-B	Without	63		G1/4	1.5 / 10	DSM-63-270-A-B

Disclaimer: The content of this document has been composed with the utmost care. However, it is possible that certain information changes over time, becomes inaccurate or incomplete. ERIKS does not guarantee that the information provided on this document is up to date, accurate and complete; the information provided is not intended to be advice. ERIKS shall never be liable for damage resulting from the use of the information provided.