

ECON® Bourdon pressure gauge Type 3664: rear connection brass mounting bracket



Characteristics

Type: 3664

Model: Bourdon tube pressure gauge

Blow-out included: No

Pressure gauge attachment: Panel mount

Process connection: External thread

Process connection material: Brass

Window material: Plastic

Protection class: IP65

Medium temperature: 0 / 60 °C

Ambient temperature: -20 / 60 °C

Application

- Industry.
- Installation technology.
- Hydraulics.

Technical Information

- Suitable for gases and liquids that do not affect the brass measuring system.
- Suitable for outdoor installation.
- Glycerine filling for damping of mechanical vibrations.
- Measuring ranges according to EN 837-1.
- Panel mounted dashboard model via bracket mounting.

Options

- Damping screw in the connection.
- Process connection NPT.

Cabinet diameter mm	Measuring range	Pressure unit	Accuracy class	Cabinet filling fluid	Connection location	Size process connection	Cabinet material	Material dial	Maximum overpressure bar	Article
63	-1 / 0	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	0	13503136
63	-1 / 3	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	3	14664760
63	-1 / 5	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	5	14664758
63	-1 / 9	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	9	14664759
63	0 / 0.6	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	0.6	14664761
63	0 / 1	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	1	14285566
63	0 / 2.5	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	2.5	13686557
63	0 / 4	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	4	13349280
63	0 / 6	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	6	13349279
63	0 / 10	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	10	13686556
63	0 / 16	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	16	13349281
63	0 / 25	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	25	12944369
63	0 / 40	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	40	12944370
63	0 / 60	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	60	14246091
63	0 / 100	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	100	13349278
63	0 / 160	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	160	14108577
63	0 / 250	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	250	13019037
63	0 / 400	bar	1.6 %	Glycerin	Back centric	1/4" BSPP[G]	Stainless steel 304	Aluminium	400	13349288

Disclaimer: The content of this document has been composed with the utmost care. However, it is possible that certain information changes over time, becomes inaccurate or incomplete. ERIKS does not guarantee that the information provided on this document is up to date, accurate and complete; the information provided is not intended to be advice. ERIKS shall never be liable for damage resulting from the use of the information provided.