

Globe valve Aluminum 1, 2 or 3-piece hydraulic impulse unit for operating the ESD valves.

Characteristics

Type: 106

Suitable for type: SOS Globe valve

Material: Aluminium

Application

ECON® Hydro impulse unit Aluminium Suitable for type: SOS

• The hydraulic impulse unit is mounted at a safe distance, in another compartment, from the ESD valve. By pulling the lever of the impulse generator the oil volume below the plunger is displaced through the transfer line to the activation cylinder of the ESD closing. The volume of oil displaced under pressure will move the piston rod of the cylinder, releasing the blockage and closing the valve.

Technical Information

• Per impulse unit, 3 ESD valves can be operated.An ESD valve on a day tank must always be operated with its own 1-piece pulse generator.





Type	Execution	Α	В	D	L
		[mm]	[mm]	[mm]	[mm]
106	1-piece	275	80	117	454
107	2-piece	275	165	117	454
108	3-piece	275	250	117	454

Execution	Article
Hydro impulse unit 1-part	12711592
Hydro impulse unit 2-part	13612115
Hydro impulse unit 3-part	13624236

Disclaimer: The content of this document has been composed with the utmost care. However, it is possible that certain information changes over time, becomes inaccurate or incomplete. ERIKS does not guarantee that the information provided on this document is up to date, accurate and complete; the information provided is not intended to be advice. ERIKS shall never be liable for damage resulting from the use of the information provided.

Page 1/1